

Product sheet



VALENA LIFE LEGRAND

Lighting+time delay ventilation switch+neutral Valena In'Matic -10 AX-250 V~

REF. 752032 | EAN. 3414970540942

[> Visit e-catalogue](#)

Product characteristics

- Valena™ IN'MATIC mechanisms - switches - Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting - Supplied with mounted dust protection transparent shield - To be equipped with Valena Life or Valena Allure cover plates and plates - Packaged in boxes
- Switches 10 AX - 250 V~Lighting + time delay ventilation switch, with neutral - Screw terminals - For switching on a fan (extractor) and a light - When the light is switched off, the fan continues for a period which can be set between 25 s and 15 min - Lighting power: - - ELV halogen with ferromagnetic or electronic transformer: 250 VA - 230 V halogen and incandescent: 250 W - Fluorescent tubes with ballast: 100 VA - Fan power: 250 VA - The switch incorporates a LED for the illumination function (locator)

Documentation

TECHNICAL DOCUMENTATION

→ [LE07428AA.pdf](#) | PDF (1.49Mo)

CAD & Design specs / BIM

 [752032_AllCATPart.stp](#) | IFC (13.68Mo)