

# Product sheet



## VALENA LIFE LEGRAND

2-gang two-way switch Valena Life - 10 AX 250 V~ - IP44 - white

REF. 752158 | EAN. 3414970459275





[> Visit e-catalogue](#)

## Product characteristics



- Valena™ Life - IP44 devices with white cover plate - Valena In'Matic mechanisms supplied with white cover plates, weatherproof membrane and support frames - To be equipped with plates - Supplied with mounted dust protection transparent shield - Flowpack packaging: robust protection to ensure optimum operation
- Switches 10AX- 250 V~ - Automatic terminals 2-gang two-way switch - White

## Documentation

### TECHNICAL DOCUMENTATION

-  F02085DE-01.pdf | PDF (1.04Mo)
-  F02085FR-01.pdf | PDF (1.04Mo)
-  LE08107AC.pdf | PDF (1.28Mo)
-  F02085EN-01.pdf | PDF (1.04Mo)

### Agreements & Certificates

-  OC / CB-FR\_711212 | (1.01Mo)
-  VDE-40044639 | (0.29Mo)

### CAD & Design specs / BIM

-  752155\_AllCATPart.stp | IFC (53.15Mo)