


Product sheet



LEGRAND

Horizontal adjustable supports kit for flush floor box, capacity 18 modules (three baskets 6 modules)

REF. 088121 | EAN. 3414970756053

> [Visit e-catalogue](#)

Product characteristics

- Baskets' height adjustable from 92mm to 122mm (from the top of the supports kit) quickly and without tool by manual locking.
- Baskets compatible with the wiring devices Legrand Mosaic and Arteur. pre - cut cables outputs to facilitate their installation.
- Equipped with four adjustable feet up to a 122mm height. Over that use the accessory : cat N° 088142 (maximum 300mm).
- kit's frame in galvanised steel for protection against corrosion.
- Baskets supports meet the IEC/EN 60670-23 standard. Moreover, with the lid of floor box closed, they offer a degree of protection IP24 (no risk of digital contact on the electrical connections, and protection against water projections)

Recommendation / Restriction

- Indoor use only.

The product's benefits

Installation

- Floor box modular to compose : matchs with your needs (type of installation, number of modules, finishes), gives time for reflexion, protects the product during the progression of the work site (the installation follows the steps of the site).

Usage

- Adapts to the surrounding environment thanks to the choice possibilities of the flush lid to associate with it : Stainless steel or Brass finish.

Avantages

- A universal range available in three sizes, adapted to any kind of floor (raised floors, screed floors) and upgradable because equipped with commons wiring devices supports (a standard floor box can become a flush one without touching the electrical connexions).
- Equipped with four mounting claws to lock its frame to the floor, the flush floor box can even so be easily installed in a raised floor.

Documentation

TECHNICAL DOCUMENTATION

- [LE09679AA-06.pdf](#) | PDF (3.23Mo)
- [F03332FR-01.pdf](#) | PDF (2.96Mo)
- [F03332EN-01.pdf](#) | PDF (3.11Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_1146.pdf](#) | PDF (0.48Mo)
- [ex223001_1147.pdf](#) | PDF (0.47Mo)
- [ex223001_1145.pdf](#) | PDF (0.12Mo)

 F03335EN-03.pdf | PDF (4.72Mo)

 F03335FR-03.pdf | PDF (4.73Mo)

CAD & Design specs / BIM

Legrand_universal_round_floor_boxes_EN.rfa | RFA (1.09Mo)

Legrand_boites_de_sol_univ_affleurant_FR.rfa | RFA (1.45Mo)

legrand_boites_de_sol_univ_vers_rde_FR.rfa | RFA (1.09Mo)

Legrand_universal_std_floor_boxes_NL.rfa | RFA (1.49Mo)

Legrand_universal_std_floor_boxes_EN.rfa | RFA (1.46Mo)

Legrand_universal_flush_floor_boxes_NL.rfa | RFA (1.45Mo)

Legrand_universal_flush_floor_boxes_EN.rfa | RFA (1.45Mo)

Legrand_universal_round_floor_boxes_NL.rfa | RFA (1.09Mo)

 3D_LG-088121.stp | IFC (20.5Mo)

legrand_boites_de_sol_univ_vers_std_FR.rfa | RFA (1.46Mo)