


# Product sheet



LEGRAND

Brass Lid and Trim of Standard box for verticals supports with 12 modules or horizontal with 18 modules

REF. 088007 | EAN. 3414970755001

[> Visit e-catalogue](#)

## Product characteristics

- Accepts all kind of coating with maximum 8mm thickness.
- Removable Lid to facilitate connections to the wiring devices
- Rigid cable exit in metal, with a retaining stop in opening position and a foam to protect cords.
- Discreet and easy opening by one hand thanks to its central button.
- Once mounted, the floor box have a global load resistance 5000N (vertical load applied through a large surface diam, 130mm)

## Recommendation / Restriction

- Indoor use only.

## The product's benefits

### Installation

- Floor box modular to compose : matchs with your needs (type of installation, number of modules, finishes), gives time for reflexion, protects the product during the progression of the work site (the installation follows the steps of the site).

### Usage

- Two possible orientations for the cable exit : Lid and Trim easily reversible to 180 degrees

### Avantages

- A universal range available in three sizes, adapted to any kind of floor (raised floors, screed floors) and upgradable because equipped with commons wiring devices supports (a standard floor box can become a flush one without touching the electrical connexions).
- Installation without tool : clips-on and unclips easily in the support kit : quick mounting and inexpensive maintenance.
- Association of metal lid robustness and brushed Brass elegance.

## Documentation

### TECHNICAL DOCUMENTATION

 F03331EN-02.pdf | PDF (4.4Mo)

 F03331FR-02.pdf | PDF (4.42Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_1143.pdf | PDF (0.46Mo)

 ex223001\_1140.pdf | PDF (0.12Mo)

→ LE09677AA-03.pdf | PDF (2.3Mo)

 F03334EN-02.pdf | PDF (7.03Mo)

 F03334FR-02.pdf | PDF (7.12Mo)

 ex223001\_1144.pdf | PDF (0.05Mo)

 ex223001\_1142.pdf | PDF (0.51Mo)

## CAD & Design specs / BIM

Legrand\_universal\_round\_floor\_boxes\_EN.rfa | RFA (1.09Mo)

Legrand\_boites\_de\_sol\_univ\_affleurant\_FR.rfa | RFA (1.45Mo)

legrand\_boites\_de\_sol\_univ\_vers\_rde\_FR.rfa | RFA (1.09Mo)

Legrand\_universal\_std\_floor\_boxes\_NL.rfa | RFA (1.49Mo)

Legrand\_universal\_std\_floor\_boxes\_EN.rfa | RFA (1.46Mo)

Legrand\_universal\_flush\_floor\_boxes\_NL.rfa | RFA (1.45Mo)

Legrand\_universal\_flush\_floor\_boxes\_EN.rfa | RFA (1.45Mo)

Legrand\_universal\_round\_floor\_boxes\_NL.rfa | RFA (1.09Mo)

legrand\_boites\_de\_sol\_univ\_vers\_std\_FR.rfa | RFA (1.46Mo)