

# Product sheet



## LEGRAND

Stainless steel Finishing plate for plastic lid of standard floor box cat N°088000

REF. 088015 | EAN. 3414970891242

> [Visit e-catalogue](#)

## Product characteristics

- Thickness 8 mm, perfectly adapted to the lid
- Easy installation thanks to two adhesive tapes
- Brushed Stainless steel
- Once mounted, the floor box have a global load resistance 500N (vertical load applied through a little surface)

## Recommendation / Restriction

- Indoor use only.

## The product's benefits

### Installation

- Floor box modular to compose : matchs with your needs (type of installation, number of modules, finishes), gives time for reflexion, protects the product during the progression of the work site (the installation follows the steps of the site).

### Usage

- Excellent daily robustness (wheel of office chair, furniture...). IK08 : Protection against choc energy until 5 joules

## Documentation


### TECHNICAL DOCUMENTATION

-  F03331EN-02.pdf | PDF (4.4Mo)
-  F03331FR-02.pdf | PDF (4.42Mo)
-  F03334EN-02.pdf | PDF (7.03Mo)
-  F03334FR-02.pdf | PDF (7.12Mo)

### CAD & Design specs / BIM

- Legrand\_universal\_round\_floor\_boxes\_EN.rfa | RFA (1.09Mo)
- Legrand\_boites\_de\_sol\_univ\_affleurant\_FR.rfa | RFA (1.45Mo)
- legrand\_boites\_de\_sol\_univ\_vers\_rde\_FR.rfa | RFA (1.09Mo)
- Legrand\_universal\_std\_floor\_boxes\_NL.rfa | RFA (1.49Mo)
- Legrand\_universal\_std\_floor\_boxes\_EN.rfa | RFA (1.46Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_1143.pdf | PDF (0.46Mo)
-  ex223001\_1140.pdf | PDF (0.12Mo)
-  ex223001\_1144.pdf | PDF (0.05Mo)
-  ex223001\_1141.pdf | PDF (0.1Mo)
-  ex223001\_1142.pdf | PDF (0.51Mo)

Legrand\_universal\_flush\_floor\_boxes\_NL.rfa | RFA (1.45Mo)

Legrand\_universal\_flush\_floor\_boxes\_EN.rfa | RFA (1.45Mo)

Legrand\_universal\_round\_floor\_boxes\_NL.rfa | RFA (1.09Mo)

legrand\_boites\_de\_sol\_univ\_vers\_std\_FR.rfa | RFA (1.46Mo)