

# Product sheet



LEGRAND

Line tap - non-shear - with feet - capacity per tap 2x50 mm<sup>2</sup> - hexagonal head

REF. 034044 | EAN. 3245060340445

[> Visit e-catalogue](#)

## Product characteristics

- Line taps and equipotential bonding connectorsLine tapsNon-shear line taps- Hexagonal head - With feet - Capacity per tap : 2 x 50 mm<sup>2</sup>- Width of slot : 9.5 max. cable Ø in mm- Overall height : 59 mm- Fixing centres : 44 mm

## Documentation

### TECHNICAL DOCUMENTATION

 F00003-01fr.pdf | PDF (0.04Mo)

 F00003-01en.pdf | PDF (0.04Mo)

 0064U92-01.pdf | PDF (0.01Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0820.pdf | PDF (0.22Mo)