

# Product sheet



LCS<sup>3</sup> LEGRAND

Patch panel 19 inch - equipped with 24 RJ45 Category 6A UTP

REF. 033770 | EAN. 3414970870681

[> Visit e-catalogue](#)

## Product characteristics

- Equipped with 4 extractable cassettes each containing 6 connectors. Cat 6A UTP RJ45 quick - connect connectors (no tools required), with 568 A/B marking.
- Equipped with rear cable guide to hold the cables.
- 19" panel - 1 U.
- Supplied with coloured labels, white yellow, blue and red.

## Recommendation / Restriction

- Compliant with ISO/IEC 11801 edition 3.0 (2017) and EIA/TIA 568 C2-1 standards

## The product's benefits

### Installation

- Front-panel and fast-snap accessibility of each individual connector provide ease and reliability for installation and maintenance. Universal and secured mounting on any cabinet or enclosure through new generation quick-fix anchorage. Automatic cassette removal by a simple button press. Hands-free cassette support during installation or maintenance while in the extracted position.

### Usage

- Daily user maintenance is rendered easy through the move-add-change management of each cassette and individual connector.


### Avantages

- Save time at both installation and in daily maintenance by taking advantage of the screwless mounting and the automatic removal of each cassette.

## Documentation

### TECHNICAL DOCUMENTATION

 S000096850FR-06.pdf | PDF (8.19Mo)

 S000096850EN-06.pdf | PDF (8.19Mo)

 LE09727AD.pdf | PDF (4.73Mo)

CAD & Design specs / BIM

### CATALOGUE PAGE & OTHERS

 ex223001\_0978.pdf | PDF (0.16Mo)

Agreements & Certificates

Flat patch panels equipped copper.rfa | RFA (0.94Mo)

Panneaux de brassages droits équipés cuivre.rfa | RFA (0.85Mo)

 AoC-4PPoE 2019-676 Ac Delta Force | (0.08Mo)

 LGRP-00626-V02.01-FR.pdf | PDF (0.96Mo)

 AoC-Composant Cat6A UTP 3P-1200837 | (0.06Mo)

 AoC-CL2\_Cat6A\_UTP\_32787\_ac1171013 | (0.08Mo)

 AoC-PL2\_Cat6A\_UTP\_32787\_ac1171012 | (0.08Mo)

 LGRP-00626-V02.01-EN.pdf | PDF (0.95Mo)