

Product sheet



LEGRAND

Internal door - for cabinets height 500 x width 400 - height 441 x width 336 mm

REF. 036360 | EAN. 3245060363604

[> Visit e-catalogue](#)

Product characteristics

- Atlantic stainless steel and Marina cabinets - internal doors
- Insulating internal doors RAL 7035 - For direct mouting in Marina cabinets , with Cat.No 0 363 69 in Atlantic metal cabinets - IP XXB - Polyester fiber glass reinforced, height 4 mm - Self - extinguishing 960°C acc. to IEC EN 60695 - 2 - 11 - Grid lines integrated on back - Centre marking on Front - Adjustable distance between cabinet door and internal door : 42 to 50 mm for Atlantic cabinets , more than 100 mm for Marina cabinets - Right or Left opening, captive hinge pins - Double bar key : 1 key for 400 to 600 mm height, 2 keys for height from 700 mm - Take key barrels and other barrels - For cabinets Height x Width : 500 x 400 mm - Dim. Height x Width : 441 x 336 mm - Usable dim. Height x Width : 406 x 270 mm

Documentation

TECHNICAL DOCUMENTATION

→ [041728-00.pdf](#) | PDF (0.74Mo)

CAD & Design specs / BIM

[036360.dwg](#) | DWG (0.05Mo)

CATALOGUE PAGE & OTHERS

[ex223001_0436.pdf](#) | PDF (0.2Mo)