

Product sheet



DPX³ 250HP LEGRAND

Circuit breaker DPX3 250HP 4 poles, rated current of 40A and S10 electronic protection unit

REF. 423515 | EAN. 3414971053090

[> Visit e-catalogue](#)

Product characteristics

- Breaking capacity of 100kA, according to EN/IEC standard 60947 - 2, suitable for protection of high power industrial installations. Rated insulation voltage of 800V. Rated impulse withstand voltage of 8kV
- Compliant with NEMA AB-1. Climatic condition according to IEC/EN 60947 - 1 Annex Q, Cat. F subject to temperature, humidity, vibration, shock and salt mist.
- Completely flexible regulation of the protection unit by dedicated App and software for thermal and magnetic currents and times Thermal protection within range of 0,4 - 1,0 of the rated current. Magnetic protection within range of 1,5 - 10 of the rated current. Equipped with earth leakage module. Earth leakage trip integrated of type A, with adjustable sensitivity of 0,03 - 0,3 - 1 - 3 Ampere and adjustable tripping of 0 - 0,3 - 1 - 3 seconds
- Can be equipped with releases (undervoltage and shunt releases) and auxiliary contacts. Can be used with rotary handles or motor operator. Locking accessories are available.
- Has different type of possible connection accessories: cage terminals, spreader and rear terminals. Is available also in a plug-in version or draw-out configuration (circuit breaker fitted with special terminals and mounted on a plug-in base).

The product's benefits

Installation

- DPX3 platform has been developed to give a new solution of protection devices for a more precise approach in power installations in order to offer the correct answer for different project needs.

Usage






- DPX3 platform provides a complete "project" approach in premium market segment, offering a range completely suitable for high power application

Advantages

- DPX3 250HP is the answer for the competition in the project sub-segment. A unique size for all versions (thermal magnetic, electronic with or without measure).
- Adjustment of I_r , I_{sd} , I_i , I_g , t_r , t_{sd} , t_g directly on the MCCB or via software/App For connection to the App add a Bluetooth communication key ref. LG-028310 Green indicator lamp. Connector for test unit Logical selectivity For 4P version: adjustment of neutral on front panel or by software or App
- EnerUp + Project App for smartphone and tablet available on Apple Store and Google Play Configuration, monitoring and management software (PCS) available for download via e-catalogue (does not require the use of Bluetooth communication key ref. LG-028310)

Documentation





TECHNICAL DOCUMENTATION

- [LE13196AA.pdf](#) | PDF (2.92Mo)
-  [EXB20072_logic_selectivity \(print\).pdf](#) | PDF (6.63Mo)
-  [F04056EN00_DPX3_250HP_ELE S10.pdf](#) | PDF (3.54Mo)
-  [EXB19026_CA_DPX3_125HP250HP_630_1600EN.pdf](#) | PDF (82.93Mo)
- [LE08866AC.pdf](#) | PDF (6.7Mo)
-  [PRT220015_GT_selectivite_logique.pdf](#) | PDF (6.38Mo)
-  [EXB21086_CA_DPX3HP125_250_DPX3630_1600FR.pdf](#) | PDF (83.49Mo)


CAD & Design specs / BIM

-  [423455.dwg](#) | DWG (0.34Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0173.pdf](#) | PDF (0.08Mo)
-  [ex223001_0192.pdf](#) | PDF (0.19Mo)
-  [ex223001_0193.pdf](#) | PDF (0.04Mo)
-  [ex223001_0191.pdf](#) | PDF (0.12Mo)

Software & configurators

-  [PowerControlStation 5.0.70.zip](#) | ZIP (52.5Mo)