

Product sheet



DX³ LEGRAND

Isolating switch DX3-IS 2 pole 20A

REF. 406432 | EAN. 3245064064323

[> Visit e-catalogue](#)

Product characteristics

- Rated current 20 A Category of use AC - 22A Rated voltage 400V~
- Can be supplied either by copper cable, prong busbar (top side or bottom side).
- Can be equipped with Legrand DX3 auxiliaries and Accessories .
- Protected against solid bodies larger than 12,5mm ("fingerproof"): IP20 according to IEC/EN 60529 standard.
- This device complies with substance-restriction requirements and has been designed in an environmentally conscious process.

Recommendation / Restriction

- This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

Documentation

TECHNICAL DOCUMENTATION

 F01479FR-01.pdf | PDF (0.48Mo)

 F01479EN-02.pdf | PDF (0.48Mo)

The product's benefits

Installation

- Fitted with DIN rail clamps, on top side and on bottom side to facilitate the installation on the DIN rail.

Usage


- Fitted with a label holder allowing a clear, visible and convenient identification of the circuit. ON and OFF indication printed on the handle respectively on red and green backgrounds for an easy identification of the status of the contacts.

CATALOGUE PAGE & OTHERS


 ex223001_0058.pdf | PDF (0.09Mo)


 ex223001_0060.pdf | PDF (0.04Mo)

CAD & Design specs / BIM

 406431.dwg | DWG (0.11Mo)

Agreements & Certificates

 NF-NF 623880A | (0.16Mo)

 VDE-40036737 | (0.26Mo)

 VDE-40036761 | (1.23Mo)

 NF-NF208_1036 | (0.53Mo)

 OC / CB-CB FR 623880C | (0.23Mo)

 OC / CB-FR_718527 | (0.41Mo)

 DC-D13_13-SELECTIVITE _FILIATION-A-3-NIVEAUX.pdf |
PDF (0.62Mo)