

Product sheet



LCS³ LEGRAND

High density preterminated fibre optic link OS2 MTP 12 fibre optic length 30m

REF. 032453 | EAN. 3414970764423

[> Visit e-catalogue](#)

Product characteristics

- OS2 single-mode 9/125µm
- Fan - out - Fan - out : spark gap for optimum resistance
- OS2 max 10Km at 10 Gigabits in full duplex mode
- LSZH (Low Smoke Zero Halogen) sheath, Colour yellow
- Length 30m

Recommendation / Restriction

- This enhanced low macro bending sensitive, low water peak fibre, gives unsurpassed bending performance. The preferred use of this low macro bendinsensitive fibre is in office installations, for patch cords, interconnection cables and for Fibre-to-the-Home networks.

The product's benefits

Installation


- A breakout module provides a secure transition between cable and tails. The cable, the furcation tubing and their strength members are securely attached to the breakout module, the 250 µm fibres are securely routed from cable into the tails.


Usage

- The outstanding bending performance of this fibre supports future compact cable management.


Documentation

TECHNICAL DOCUMENTATION

 S000101590EN-03.pdf | PDF (0.44Mo)

 S000101590FR-03.pdf | PDF (0.49Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0999.pdf | PDF (0.13Mo)