

Product sheet



DX³ LEGRAND

RCCB DX3 2 pole 100A type AC 300mA screw terminals

REF. 411528 | EAN. 3245064115285

> [Visit e-catalogue](#)

Product characteristics

- Screw terminals top side for supply by cables. Load connection bottom side by screw terminals for cables.
- AC - type for the detection of AC residual currents.
- Width = 2 modules
- Fitted with a test button, to be used frequently to check the tripping of the residual current function. This device complies with substance-restriction requirements and has been designed in an environmentally conscious process. Protected against solid bodies larger than 12,5mm ("fingerproof"): IP20 according to IEC/EN 60529 standard.

Recommendation / Restriction

- This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

Documentation

TECHNICAL DOCUMENTATION

F01316EN-03.pdf | PDF (0.73Mo)

F01316FR-03.pdf | PDF (0.79Mo)

LE03774AB.pdf | PDF (1.99Mo)

The product's benefits

Installation

- Fitted with DIN rail clamps, on top side and on bottom side to facilitate the installation on the DIN rail.

Usage


- Fitted with a label holder allowing a clear, visible and convenient identification of the circuit. On and OFF indication printed on the handle respectively on red and green backgrounds for an easy identification of the status of the RCCB

CATALOGUE PAGE & OTHERS


ex223001_0059.pdf | PDF (0.12Mo)


ex223001_0060.pdf | PDF (0.04Mo)


CAD & Design specs / BIM

 411505.dwg | DWG (0.16Mo)

Agreements & Certificates

 NF-NF012_3245 | (0.18Mo)

 VDE-40032163 | (0.51Mo)

 LGRP-00366-V02.01-EN.pdf | PDF (0.64Mo)

 AENOR-030/002247 | (0.82Mo)

 OC / CB-CB FR_713498/M1 | (2.3Mo)

 LGRP-00366-V02.01-FR.pdf | PDF (0.6Mo)

 DC-D13_13-SELECTIVITE _FILIACTION-A-3-NIVEAUX.pdf | PDF (0.62Mo)