

# Product sheet



## LEGRAND

RCD DX<sup>3</sup>-ID - 2P 230 V~ - 25 A - 100 mA - AC type

REF. 411514 | EAN. 3245064115148

[> Visit e-catalogue](#)

## Product characteristics

- RCCBs - DX<sup>3</sup> - ID - residual current circuit breakers 16 A to 100 A - AC, A, F and B types - Conform to IEC 61008 - 1, IEC 62423 (B type and F type) - Compatible with prong - type and fork type supply busbars - AC type : detect sinusoidal AC residual currents - A type : detect sinusoidal AC and pulsating DC residual currents - F type (High immunity) : detect AC and pulsating DC residual currents - Enhanced immunity to unwanted tripping in disturbed environments - Detection of high frequency fault currents - B type : detect sinusoidal AC, pulsating DC and smooth DC residual currents - Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries and motorised controls
- 2-pole 230 V~AC type - Sensitivity : 100 mA - Nominal Rating In : 25 A - Number of modules : 2

## Documentation

### TECHNICAL DOCUMENTATION

 F01316EN-04.pdf | PDF (0.9Mo)

 LE03774AB.pdf | PDF (1.99Mo)

 F01316FR-04.pdf | PDF (0.76Mo)

### CAD & Design specs / BIM

 411505.dwg | DWG (0.16Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0059.pdf | PDF (0.12Mo)

 ex223001\_0060.pdf | PDF (0.04Mo)

### Agreements & Certificates

 LGRP-00366-V02.01-FR.pdf | PDF (0.6Mo)

 NF-NF012\_3245 | (0.18Mo)

 LGRP-02038-V01.01-FR.pdf | PDF (0.77Mo)

 VDE-40032163 | (0.51Mo)

 LGRP-00366-V02.01-EN.pdf | PDF (0.64Mo)

 OC / CB-CB FR\_713498/M1 | (2.3Mo)