

Product sheet



LINKEO LEGRAND

Intelligent PDU, metered (Base version), 19 inch, 1 phase 16A, 8 C13 outlets with cord locking, C20 inlet

REF. 646100 | EAN. 3414972245852

[> Visit e-catalogue](#)

Product characteristics

- 1 phase - 16A - Max power 3,7kW
- 8 C13 outlets, with cord locking system
- Metering at inlet and circuit level with +/- 1% accuracy (Voltage, Current, Active Power, Apparent Power, Energy, Power Factor)
- To be linked with a Node PDU version to enable remote access to all measurements and alerts.
- C20 inlet

Recommendation / Restriction

- A Base PDU version needs to be linked with a Node PDU version to enable remote access to all measurements and alerts.

The product's benefits

Installation

- Easy installation thanks to the 330° rotating cable input for a perfect orientation of the cable and no interference in the cabinet. Numbered outlets to ease the identification of each server. Supplied with 2 sets of metal fixings: button for screwless fixing, or standard screw-type brackets.

Usage


- Reduce your CAPEX and deploy intelligent PDUs without the need to have a PDU controller in every unit. Reduce your OPEX by daisy-chaining up to 31 base PDUs downstream to a node PDU to save switch ports connections. User-friendly and responsive Web User Interface. Metering, outlet Control and peripherals data at glance. Easy to configure. Data aggregation capabilities in DCIM.


Avantages

- 2 levels of alerts physically visible on the PDU (LED bar) and remotely (web interface and email/sms alert configuration)
- Possibility to add up to 8 wireless sensors (temperature, humidity...) for environmental monitoring. Using wireless sensors reduce deployment and maintenance time.
- Upgradeable to a Node PDU version by adding a Node controller (ref. 646130)

Documentation

TECHNICAL DOCUMENTATION

 [FT-646100-FR-02.pdf](#) | PDF (0.89Mo)

 [FT-646100-EN-02.pdf](#) | PDF (0.89Mo)

 [LE13286AD.pdf](#) | PDF (3.55Mo)


CAD & Design specs / BIM

[PDU metered 1U.rfa](#) | RFA (0.88Mo)

[Metered PDU 1U.rfa](#) | RFA (0.88Mo)

Software & configurators


 [PDU_LDC_040031-49324_ReleaseNotes.pdf](#) | PDF (0.23Mo)

 [PDU_LDC_040031-49324_Firmware.bin](#) | BIN (16.21Mo)


CATALOGUE PAGE & OTHERS

 [ex223001_1040.pdf](#) | PDF (0.37Mo)

Agreements & Certificates

 [LGRP-01652-V03.01-EN.pdf](#) | PDF (1.72Mo)

 [Decl. UE RED-AT 50583108 0001](#) | (0.6Mo)

 [LGRP-01652-V03.01-FR.pdf](#) | PDF (1.69Mo)